

## **Product information**

## 97 54 24

## **Crimping Pliers for micro plugs**

Parallel crimping



- Parallel crimping performance to satisfy the particularly high standards of small connectors
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatiguereduced operation
- Crimping pliers for other mini plugs such as HD 22, Modu IV, Micro Timer, MQS ... on request
- Special quality chrome vanadium electric steel, oil-hardened

General

oonorai	
Article No.	97 54 24
EAN	4003773060215
Pliers	burnished
Handles	with multi-component grips
Weight	305 g
Dimensions	190 x 60 x 34 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

## **Technical details**

A Har

Application	D Sub; HD 20; HDE plug
Capacity in square millimetres	0.03 — 0.56 mm²
Number of crimping positions	3
AWG	32 — 20

technical change and errors excepted



