

Product information

97 55 04

Self-Adjusting Crimping Pliers for wire • ferrules


With lateral access



- · Narrow handle width and improved ergonomics
- Square compression now for wire ferrules up to 16 mm²
- Square compression for ideal contact surfaces in the clamp connection
- Suitable in particular for all twin wire ferrules up to 2 x 4 mm² or 2 x AWG 12
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of wire ferrules required
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatiguereduced operation
- Handy shape and low weight provide high operation comfort
- Special quality chrome vanadium electric steel, oil-hardened

| General | |
|-----------------|----------------------------|
| Article No. | 97 55 04 |
| EAN | 4003773084853 |
| Pliers | chrome-plated |
| Head | chrome-plated |
| Handles | with multi-component grips |
| Weight | 459 g |
| Dimensions | 180 x 77 x 21 mm |
| REACH compliant | contains SVHC |
| RoHS compliant | not applicable |

Technical details



technical change and errors excepted

KNIPEX Quality – Made in Germany





