

Product information

97 59 14

Locator for 97 52 14

- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
 Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatiguereduced operation
- Good handling due to 20° angled head, low weight and short design
- Special quality chrome vanadium electric steel, oil-hardened



General

| General | |
|-----------------|-----------------------|
| Article No. | 97 59 14 |
| EAN | 4003773026976 |
| Weight | 10 g |
| Dimensions | 20 x 10 mm |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

technical change and errors excepted