

Product information

97 61 145 A

Crimping Pliers for wire ferrules

- For crimping wire ferrules according to DIN 46228 parts 1 + 4 in the range from 0.25 up to 2.5 mm²
- Crimping in marked trapezoidal dies for reliable connections between the sleeve and the conductor
- Vanadium electric steel; forged, oil-hardened





General	
Article No.	97 61 145 A
EAN	4003773035558
Head	polished
Handles	plastic coated
Weight	140 g
Dimensions	145 x 52 x 13 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details Application Capacity in square millimetres Number of crimping positions Wire ferrules 0.25 — 2.5 mm² 4

24 — 14

technical change and errors excepted

AWG