

## Product information


# 97 61 145 F

## Crimping Pliers for wire ferrules

- For crimping wire ferrules according to DIN 46228 parts 1 + 4 in the range from 0.25 up to 2.5 mm<sup>2</sup>
- Crimping in marked trapezoidal dies for reliable connections between the sleeve and the conductor
- Vanadium electric steel; forged, oil-hardened



General	
Article No.	97 61 145 F
EAN	4003773043980
Head	polished
Handles	plastic coated
Weight	140 g
Dimensions	145 x 49 x 13 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
	
Application	Wire ferrules
Capacity in square millimetres	0.25 — 2.5 mm <sup>2</sup>
Number of crimping positions	4
AWG	24 — 14

*technical change and errors excepted*