

## **Product information**

## 97 72 180

## **Crimping Pliers for wire ferrules**



- Light and slim design
- Also as VDE version
- Easy crimping due to optimised transmission ratio
- For crimping wire ferrules according to DIN 46228 parts 1 + 4 from 0.25 to 16 mm<sup>2</sup>
- Crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened

General	
Article No.	97 72 180
EAN	4003773060185
Head	polished
Handles	with multi-component grips
Weight	242 g
Dimensions	180 x 51 x 22 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

## **Technical details**



Application	Wire ferrules
Capacity in square millimetres	0.25 — 16.0 mm²
Number of crimping positions	9
AWG	24 — 6

technical change and errors excepted

