

Product information

97 78 180 T

Crimping Pliers for wire ferrules

IEC 60900 DIN EN 60900





- Light and slim design
- Also as VDE version
- Easy crimping due to optimised transmission ratio
- Pliers with integrated, insulated tether attachment point for a tool tether
- For crimping wire ferrules according to DIN 46228 parts 1 + 4 from 0.25 to 16 mm²
- Crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened



General	
Article No.	97 78 180 T
EAN	4003773081531
Head	polished
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	260 g
Dimensions	180 x 54 x 28 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details



Application	Wire ferrules
Capacity in square millimetres	0.25 — 16.0 mm ²
Number of crimping positions	9
AWG	24 — 6

technical change and errors excepted

KNIPEX Quality – Made in Germany



