

Product information

97 99 356

Wire ferrules with plastic collar

DIN 46228-4: 2020-03

- Nominal size: 6 mm²
- Content: 100 pieces
- Colour: yellow
- Insertion funnel made of polypropylene
- Heat resistant up to 105°C
- Material: E-Cu
- Surface electro tin plated
- Minimum coating thickness 3µm



General	
Article No.	97 99 356
EAN	4003773076575
Standard	DIN 46228-4: 2020-03
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cable	6 mm ²
AWG	10
Colour	Yellow
L1	26 mm
L2	18 mm
d1	3.5 mm
d2	6.3 mm
S1	0.2 mm
S2	0.3 mm
Quantity	100
Insulation	PP
Material	Copper
Surface	Tinned

Technical details



technical change and errors excepted