

## Product information

**97 99 357**

### Wire ferrules with plastic collar

DIN 46228-4: 2020-03

- Nominal size: 10 mm<sup>2</sup>
- Content: 100 pieces
- Colour: red
- Insertion funnel made of polypropylene
- Heat resistant up to 105°C
- Material: E-Cu
- Surface electro tin plated
- Minimum coating thickness 3µm



General	
Article No.	97 99 357
EAN	4003773076582
Standard	DIN 46228-4: 2020-03
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cable	10 mm <sup>2</sup>
AWG	8
Colour	Red
L1	28 mm
L2	18 mm
d1	4.5 mm
d2	7.6 mm
S1	0.2 mm
S2	0.4 mm
Quantity	100
Insulation	PP
Material	Copper
Surface	Tinned

Technical details



*technical change and errors excepted*