

## Product information

**97 99 398**

### Non-insulated wire ferrules

100 pieces each

DIN 46228-4: 2020-03

- Nominal size: 16 mm<sup>2</sup>
- Content: 100 pieces
- Non-insulated
- Material: E-Cu
- Surface electro tin plated
- Minimum coating thickness 3µm



#### General

Article No.	97 99 398
EAN	4003773076780
Standard	DIN 46228-4: 2020-03
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

#### Technical details

Cable	16 mm <sup>2</sup>
AWG	6
L	12 mm
d1	5.8 mm
d2	7.5 mm
S	0.2 mm
Quantity	100
Material	Copper
Surface	Tinned

Technical details



*technical change and errors excepted*