

Product information

98 00 1/2"

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Open-end wrench

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

General	
Article No.	98 00 1/2"
EAN	4003773019879
Weight	70 g
Dimensions	32 x 11 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Width across flats S	1/2 Inch
Length l max.	139.7 mm
Head thickness a max.	6.5 mm
Head width b max. mm	34 mm



technical change and errors excepted