

## Product information

# 98 00 1/4"

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

## Open-end wrench

IEC 60900 DIN EN 60900




⚡ 1000 V ♻️

### General

Article No.	98 00 1/4"
EAN	4003773019886
Weight	32 g
Dimensions	17 x 7 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Width across flats S	1/4 Inch
Length l max.	108 mm
Head thickness a max.	4 mm
Head width b max. mm	20 mm



*technical change and errors excepted*