

Product information

98 00 15

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Open-end wrench

IEC 60900 DIN EN 60900



⚡ 1000 V ♻️

General

Article No.	98 00 15
EAN	4003773019954
Weight	80 g
Dimensions	35 x 12 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats	15 mm
Length l max.	145 mm
Head thickness a max.	7 mm
Head width b max. mm	37 mm



technical change and errors excepted

