

Product information

98 00 22

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Open-end wrench

IEC 60900 DIN EN 60900



⚡ 1000 V ♻️

General

Article No.	98 00 22
EAN	4003773020004
Weight	216 g
Dimensions	53 x 17 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats	22 mm
Length l max.	190 mm
Head thickness a max.	9 mm
Head width b max. mm	52 mm



technical change and errors excepted

