

Product information

98 00 24

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Open-end wrench

IEC 60900 DIN EN 60900




⚡ 1000 V ♻️

General

Article No.	98 00 24
EAN	4003773020011
Weight	290 g
Dimensions	54 x 19 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats	24 mm
Length l max.	210 mm
Head thickness a max.	9 mm
Head width b max. mm	56 mm



technical change and errors excepted

