

Product information

98 00 3/4"

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened


Open-end wrench

IEC 60900 DIN EN 60900



⚠ 1000 V ⚡

General	
Article No.	98 00 3/4"
EAN	4003773020035
Weight	164 g
Dimensions	42 x 11 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Width across flats S	3/4 Inch
Length l max.	190.5 mm
Head thickness a max.	9 mm
Head width b max. mm	47 mm



technical change and errors excepted