

Product information

98 00 3/8"

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Open-end wrench

IEC 60900 DIN EN 60900




⚠ 1000 V ⚡

General

Article No.	98 00 3/8"
EAN	4003773020042
Weight	37 g
Dimensions	25 x 7 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats S	3/8 Inch
Length l max.	108 mm
Head thickness a max.	5 mm
Head width b max. mm	27 mm



technical change and errors excepted