

Product information

98 00 9/16"

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened


Open-end wrench

IEC 60900 DIN EN 60900



⚡ 1000 V ♻️

General	
Article No.	98 00 9/16"
EAN	4003773020110
Weight	102 g
Dimensions	35 x 12 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Width across flats S	9/16 Inch
Length l max.	152.4 mm
Head thickness a max.	6.5 mm
Head width b max. mm	35 mm



technical change and errors excepted