

Product information

98 01 10

- Cranked
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Box Wrench

IEC 60900 DIN EN 60900



⚡ 1000 V Ⓞ

General

Article No.	98 01 10
EAN	4003773020196
Weight	75 g
Dimensions	15 x 26 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats S	10 mm
Length l max.	160 mm
Head thickness a max.	9 mm
Depth of crank h max.	20 mm
Head width b max. mm	17 mm



technical change and errors excepted

