

Product information

98 01 19

- Cranked
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Box Wrench

IEC 60900 DIN EN 60900



⚡ 1000 V Ⓞ

General

Article No.	98 01 19
EAN	4003773020295
Weight	245 g
Dimensions	22 x 42 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats S	19 mm
Length l max.	225 mm
Head thickness a max.	14 mm
Depth of crank h max.	28 mm
Head width b max. mm	30 mm



technical change and errors excepted

