

Product information

98 03 05

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Nut Driver

With screwdriver handle

IEC 60900 DIN EN 60900



⚡ 1000 V ♻️

General

Article No.	98 03 05
EAN	4003773071686
Pliers	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	70 g
Dimensions	230 x 30 x 30 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats S	5.0 mm
Handle length max.	107 mm
Head dia. d	10 mm
Blade length	125 mm
VDE tested	ja

technical change and errors excepted