

Product information

98 03 11

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Nut Driver

With screwdriver handle

IEC 60900 DIN EN 60900



⚡ 1000 V Ⓞ

General

Article No.	98 03 11
EAN	4003773026136
Pliers	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	148 g
Dimensions	237 x 35 x 32 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats S	11.0 mm
Handle length max.	112 mm
Head dia. d	19 mm
Blade length	125 mm
VDE tested	ja

technical change and errors excepted