

Product information

98 13 25

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdriver for hexagon socket screws

IEC 60900 DIN EN 60900



⚡ 1000V ○

General

Article No.	98 13 25
EAN	4003773026334
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	32 g
Dimensions	177 x 25 x 23 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Blade length	75.0 mm
Width across flats S	2.5 mm
Length of non-insulated blade	15.0 mm
Handle length	102 mm
VDE tested	yes



technical change and errors excepted