

Product information

98 13 50

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdriver for hexagon socket screws

IEC 60900 DIN EN 60900



⚠ 1000 V ○

General

| | |
|-----------------|---|
| Article No. | 98 13 50 |
| EAN | 4003773026365 |
| point | burnished |
| Handles | insulating multi-component handle, VDE-tested |
| Weight | 82 g |
| Dimensions | 187 x 35 x 33 mm |
| Standard | DIN EN 60900 IEC 60900 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|-------------------------------|---------|
| Blade length | 75.0 mm |
| Width across flats S | 5.0 mm |
| Length of non-insulated blade | 15.0 mm |
| Handle length | 112 mm |
| VDE tested | yes |



technical change and errors excepted