

## Product information

# 98 20 65 SL

## Screwdriver (Slim) for slotted screws

- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

IEC 60900 DIN EN 60900



⚡ 1000V Ⓞ

General	
Article No.	98 20 65 SL
EAN	4003773079743
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	105 g
Dimensions	262 x 35 x 32 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Blade length	150 mm
Length of non-insulated blade	15 mm
Handle length	112 mm
Blade width	6.5 mm
Blade thickness	1.2 mm
VDE tested	yes

*technical change and errors excepted*