

## Product information

**98 24 00**

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

### Screwdriver for cross recessed screws

Phillips®

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

General	
Article No.	98 24 00
EAN	4003773026433
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	32 g
Dimensions	162 x 25 x 24 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Size	PH0
Blade length	60 mm
Handle length	102 mm
Blade Ø	3.0 mm
Length of non-insulated blade	15 mm
VDE tested	yes

*technical change and errors excepted*

*Phillips® is a registered trademark of Phillips Screw Company*