

Product information

98 24 01 SLS

(Slim) PlusMinus screwdriver

Phillips®

IEC 60900 DIN EN 60900

- Driving tips for PlusMinus profile screws
- Use with electronics installation components, e.g. automatic circuit breakers
- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000V ⚡

General	
Article No.	98 24 01 SLS
EAN	4003773081036
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	56 g
Dimensions	187 x 28 x 30 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Size	PH/S 1
Blade length	80 mm
Handle length	107 mm
Length of non-insulated blade	15 mm
VDE tested	yes

technical change and errors excepted

Phillips® is a registered trademark of Phillips Screw Company



