

Product information

98 24 01 SL

Screwdriver (Slim) for cross-recessed screws

Phillips®

IEC 60900 DIN EN 60900

- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000 V ⚡

General

Article No.	98 24 01 SL
EAN	4003773079750
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	58 g
Dimensions	187 x 30 x 30 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Size	PH1
Blade length	80 mm
Handle length	107 mm
Length of non-insulated blade	15 mm
VDE tested	yes

technical change and errors excepted

Phillips® is a registered trademark of Phillips Screw Company