

Product information

98 24 04

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdriver for cross recessed screws

Phillips®

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

General

Article No.	98 24 04
EAN	4003773026471
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	244 g
Dimensions	320 x 37 x 36 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Size	PH4
Blade length	200 mm
Handle length	120 mm
Blade Ø	10.0 mm
Length of non-insulated blade	18 mm
VDE tested	yes

technical change and errors excepted

Phillips® is a registered trademark of Phillips Screw Company