

Product information

98 25 01 SL

Screwdriver (Slim) for cross-recessed screws

Pozidriv®

IEC 60900 DIN EN 60900

- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000 V ⚡

| General | |
|-----------------|---|
| Article No. | 98 25 01 SL |
| EAN | 4003773079774 |
| point | burnished |
| Handles | insulating multi-component handle, VDE-tested |
| Weight | 56 g |
| Dimensions | 187 x 28 x 30 mm |
| Standard | DIN EN 60900 IEC 60900 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

| Technical details | |
|-------------------------------|--------|
| Size | PZ1 |
| Blade length | 80 mm |
| Handle length | 107 mm |
| Length of non-insulated blade | 15 mm |
| VDE tested | yes |

technical change and errors excepted

Pozidriv® is a registered trademark of European Ind. Serv. Ltd.