

Product information

98 25 02 SLS

(Slim) PlusMinus screwdriver

Pozidriv®

IEC 60900 DIN EN 60900

- Driving tips for PlusMinus profile screws
- Use with electronics installation components, e.g. automatic circuit breakers
- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000 V ⚡

General	
Article No.	98 25 02 SLS
EAN	4003773081067
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	89 g
Dimensions	212 x 33 x 35 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Size	PZ/S 2
Blade length	100 mm
Handle length	118 mm
Length of non-insulated blade	18 mm
VDE tested	yes

technical change and errors excepted

Pozidriv® is a registered trademark of European Ind. Serv. Ltd.

