

Product information

98 25 02 SL

Screwdriver (Slim) for cross-recessed screws

Pozidriv®

IEC 60900 DIN EN 60900

- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000V ⚡

General	
Article No.	98 25 02 SL
EAN	4003773079781
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	90 g
Dimensions	212 x 35 x 32 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Size	PZ2
Blade length	100 mm
Handle length	112 mm
Length of non-insulated blade	18 mm
VDE tested	yes

technical change and errors excepted

Pozidriv® is a registered trademark of European Ind. Serv. Ltd.