

Product information

98 47 11/16"


- For imperial hexagonal head screws
- Basic tool chrome-plated
- With double-hex
- Chrome Vanadium steel

12-Point Socket

With internal square 1/2"

IEC 60900 DIN EN 60900



⚡ 1000 V 

General

Article No.	98 47 11/16"
EAN	4003773020905
Weight	88 g
Dimensions	55 x 28 x 28 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Square drive	1/2 Inch
Ø of effective tool side d max.	28.2 mm
Width across flats S	11/16 Inch



technical change and errors excepted