

Product information

99 01 220

Concreters' Nipper

(Concreter's Nippers or Fixer's Nippers)

DIN ISO 9242

- To twist and cut wire in one operation: fast, reliable and economical
- Cutting edges additionally hardened; cutting edge hardness approx.
 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened





| General | |
|-----------------|-----------------------|
| Article No. | 99 01 220 |
| EAN | 4003773021469 |
| Pliers | black atramentized |
| Head | polished |
| Handles | plastic coated |
| Weight | 335 g |
| Dimensions | 220 x 48 x 15 mm |
| Standard | DIN ISO 9242 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

| Technical details | |
|--|----------|
| Cutting capacities medium hard wire (diameter) | Ø 2.4 mm |
| Cutting capacities hard wire (diameter) | Ø 1.6 mm |

technical change and errors excepted





KNIPEX Quality – Made in Germany





