

Product information

99 01 280

Concreters' Nipper

(Concreter's Nippers or Fixer's Nippers)

DIN ISO 9242

- To twist and cut wire in one operation: fast, reliable and economical
- Cutting edges additionally hardened; cutting edge hardness approx.
 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened





General	
Article No.	99 01 280
EAN	4003773021490
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	480 g
Dimensions	280 x 53 x 26 mm
Standard	DIN ISO 9242
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 2.8 mm
Cutting capacities hard wire (diameter)	Ø 1.8 mm

technical change and errors excepted





KNIPEX Quality – Made in Germany









