

Product information

99 01 300

- To twist and cut wire in one operation: fast, reliable and economical
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

Concreters' Nipper

(Concreter's Nippers or Fixer's Nippers)

DIN ISO 9242



General

Article No.	99 01 300
EAN	4003773014416
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	548 g
Dimensions	300 x 52 x 16 mm
Standard	DIN ISO 9242
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 3.1 mm
Cutting capacities hard wire (diameter)	Ø 1.8 mm

technical change and errors excepted



