



## BE 18 LTX 6

- Fast and handy cordless drill with high precision for drilling into metal
- Collar (Ø 43 mm) for versatile use
- Integrated working light to illuminate the contact area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Overload protection: protects the motor from overheating
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

<b>Order no.</b>	<b>600261890</b>
<b>EAN code</b>	<b>4007430263520</b>
Battery voltage	18 V
Maximum torque	4 Nm // 35 in-lbs
Drill Ø steel	6 mm / 1/4 "
Drill-Ø soft wood	12 mm / 1/2 "
No-load speeds	0 - 5000 rpm
Chuck capacity	1 - 10 mm // 1/32 - 3/8 "
Weight without battery pack	1.2 kg / 2.6 lbs
Weight with battery pack	1.6 kg / 3.5 lbs

### Scope of delivery

Futuro Plus keyless chuck with metal sleeve, Open-jawed spanner, without battery pack, without charger