



GVPB 18 LTX BL 11-28

- Slim cordless die grinder with dead man function and long grinding spindle for particularly safe working, also in hard-to-reach places
- High degree of user safety thanks to paddle switch with dead man function and fast brake for fast stop of the tool being used (< 1 sec)
- Variable speed setting for working with different materials
- Particularly slim handle area for optimum handling and low-fatigue working
- Spindle lock for simple change of tools
- Powerful like a 1,100 Watt mains-powered tool thanks to efficient, service-free Brushless motor
- Electronic overload protection, soft start and restart protection
- Rubber cap for comfortable and safe working
- Battery pack can be rotated in 90° steps for best ergonomics in any working position
- Easy-to-clean dust protection filter protects motor from coarse particles
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600827850
EAN code	4061792247314
Battery voltage	18 V
No-load speed	8000 - 28000 rpm
Collar diameter	43 mm / 1 11/16 "
Collet chuck bore	6 mm / 0.2362 "
Weight without battery pack	1.4 kg / 3.1 lbs
Weight with battery pack	2.1 kg / 4.6 lbs

Scope of delivery

Collet 6 mm, Protective rubber cap, Dust protection filter, Open-jawed spanner, without battery pack, without charger