



GVB 18 LTX BL 11-28 Compact

- Compact, light cordless die grinder in short design for deburring, milling, grinding and cutting
- Variable speed setting for working with different materials
- Particularly slim handle area for optimum handling and low-fatigue working
- High degree of user safety thanks to fast brake for quick stop of the tool being used (< 1 sec)
- Powerful like a 1,100 Watt mains-powered tool thanks to efficient, service-free Brushless motor
- Electronic overload protection, soft start and restart protection
- Battery pack can be rotated in 90°steps for best ergonomics in any working position
- Easy-to-clean dust protection filter protects motor from coarse particles
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600828850
EAN code	4061792247345
Battery voltage	18 V
No-load speed	8000 - 28000 rpm
Collar diameter	43 mm / 1 11/16 "
Collet chuck bore	6 mm / 0.2362 "
Weight without battery pack	1.1 kg / 2.4 lbs
Weight with battery pack	1.8 kg / 4 lbs

Scope of delivery

Collet 6 mm, Dust protection filter, 2 open-jawed spanners, without battery pack, without charger