



MS 18 LTX 15

- Handy and safe cordless pruning saw, ideal for cutting back trees and shrubs as well as for cuttings
- In combination with the MS telescopic handle (accessory), the mini motor saw can be used like a pole pruner
- Constantly high chain speed under load for fast sawing progress
- Up to 60 powerful cuts into hard wood Ø 80 mm with one battery pack charge (Li-Power battery pack 18 V/2.0 Ah)
- Safe working thanks to guard, grip protection and safety switch against unintentional starting
- Simple handling thanks to compact size, low weight and rubberised handle areas
- Low kickback chain for easy, safe cuts and low vibrations
- Easy changing and tensioning of the saw chain thanks to quick-closure and the tensioning tool stored on the housing
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600856840
EAN code	4061792245419

Battery voltage	18 V
Track length	15 cm / 6 "
Cutting length	15 cm / 6 "
Max chain speed	5 m/s / 16.4 ft/s
Saw chain tooth shape	semi-chisel
Saw chain tooth division	1/4"
Drive link thickness	1.1 mm / 0.043 "
Number of drive links	39
Weight without battery pack	1.6 kg / 3.5 lbs

Scope of delivery

Saw rail 15 cm, Saw chain 15 cm (1/4" LP / 1.1 mm), Saws chain protection, Bio sawing chain lubrication oil 100 ml, Hexagonal wrench with spherical head, metaBOX 145 L, without battery pack, without charger