



PowerMaxx BS 12 BL Q

- Brushless drill/screwdriver with optimal power for demanding applications
- The Metabo 12 Volt class - lightweight, yet powerful
- Metabo Quick System: quick change of bit retainer and bits, for flexible working
- Integrated LED work light with night light function for optimal brightness in the work area
- Handy belt hook and bit holder can be fixed either on the right or left side

Order no.	601045850
EAN code	4061792237438
Battery voltage	12 V
Maximum torque, soft	20 Nm / 177 in-lbs
Maximum torque, hard	45 Nm / 398.3 in-lbs
Adjustable torque	0.5 - 5 Nm // 4.4 - 44.3 in-lbs
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	35 mm / 1.4 "
No-load speeds	0 - 450 / 0 - 1600 rpm
Chuck capacity	1.5 - 10 mm // 1/16 - 3/8 "
Weight without battery pack	0.8 kg / 1.8 lbs

Scope of delivery

Quick-change chuck, Belt hook and bit case, without battery pack, without charger