



PowerMaxx SB 12 BL

- Brushless cordless hammer drill with extremely compact design for universal application areas
- The Metabo 12 Volt class - lightweight, yet powerful
- Hammer drill function for drilling in masonry
- Integrated LED work light with night light function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side

Order no.	601046850
EAN code	4061792237445
Type of battery pack	Li-Power
Battery voltage	12 V
Maximum torque, soft	20 Nm / 177 in-lbs
Maximum torque, hard	45 Nm / 398.3 in-lbs
Adjustable torque	0.5 - 5 Nm // 4.4 - 44.3 in-lbs
Drill-Ø masonry	10 mm / 3/8 "
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	35 mm / 1.4 "
No-load speed	0 - 450 / 1600 rpm
Maximum impact rate	21000 bpm
Chuck capacity	1.5 - 10 mm // 1/16 - 3/8 "
Weight without battery pack	0.9 kg / 1.9 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, without battery pack, without charger