



KT 66 BL

- Plunge cut circular saw with brushless motor for powerful plunge cuts and precise cuts up to a depth of 66 mm (!)
- Adjustable fit without play on the guide rails from Metabo and other manufacturers for precise cutting results.
- Versatile application thanks to variable speed for different materials
- Double guide for precise setting of the cutting depth with and without guide rail
- With undercut function for precise transitions, 0° and 45° position readjustable for highest cutting precision
- Fast and easy changing of the sawblade with lever for locking plunge position and spindle stop
- Sawing close to wall possible
- Viewing window in the guard for precise cutting guidance
- Fast brake stops the saw blade quickly and improves safety
- Low-dust sawing thanks to large-volume dust bag or by connecting a vacuum cleaner
- Sawdust ejection nozzle for any working position can be rotated and locked individually
- Practical parallel guide available as accessory (order no. 628029000)

Order no. EAN code	601166500 4061792236783
Rated input power	1200 W
Maximum cutting depth at 90°	66 mm / 2 19/32 "
Maximum cutting depth at 45°	43 mm / 1 11/16 "
Max. cutting depth with guide rail	61 mm / 2 13/32 "
Saw blade Ø x bore	165 x 20 mm // 6 1/2 x 5/8 "
Swivel range from / to:	- 1 / + 46 °
No-load speed	2250 - 5000 rpm
Weight (without power cable)	4.9 kg
Cable length	4 m

Scope of delivery

Saw blade "precision cut wood - classic" 165x20 Z42 WZ 5°, Dust collection bag, Hexagonal wrench, meta-BOX 340