



## LD 30

- Quick measurements and simple operation
- Certified according to ISO 16331-1: guaranteed measurement quality for accuracy and range
- Handy, robust device with impact-proof housing and soft grip material
- Energy-saving thanks to automatic shutdown
- LC display with large digits for good legibility

Order no.	606162000
EAN code	4007430284709
Laser class	2
Wavelength	635 nm
Light output	< 1 mW
Measurement range	0.2 - 30 m // 0.7 - 98 ft
Measuring accuracy	± 3 mm / ± 1/8 "
Number of measurements per battery charge	5000
Protection type IP	IP 54
Weight (with batteries)	0.1 kg / 0.22 lbs
Laser functions	Length / Area / Volume / Continuous measurement (tracking)

### Scope of delivery

Belt pouch, 2 Batteries AAA 1.5 V (LR03)