



LD 60

- Quick measurements and simple operation
- Certified according to ISO 16331-1: guaranteed measurement quality for accuracy and range
- Handy, robust device with impact-proof housing and soft grip material
- Energy-saving thanks to automatic shutdown
- Illuminated LC display for good readability, even in poor light conditions
- Signal tone after measurement to avoid errors
- Flexible application range by switching the measurement reference (front / rear)

Order no.	606163000
EAN code	4007430284716
Laser class	2
Wavelength	635 nm
Light output	< 1 mW
Measurement range	0.05 - 60 m // 0.2 - 197 ft
Measuring accuracy	± 1.5 mm / ± 1/16 "
Number of measurements per battery charge	5000
Protection type IP	IP 40
Weight (with batteries)	0.11 kg / 0.24 lbs
Laser functions	Length / Area / Volume / Continuous measurement (tracking) / Pythagoras 1 / Pythagoras 2 / Minimum tracking / Maximum tracking

Scope of delivery

Belt pouch, 2 Batteries AAA 1.5 V (LR03)