



## LSV 5-225 Comfort + ASR 35 L ACP Set with 25 hook and loop sanding sheets P 120

- System solution for comfortable sanding of primed surfaces on walls or ceilings with effective extraction
- Long-neck sander LSV 5-225 Comfort: optimum balance when working, as the centre of gravity of the machine is not at the head. Extraction through the housing without hose for maximum flexibility of the sanding head. With variable length adjustment: can be shortened or extended quickly and easily for narrow rooms or high ceiling rooms. Optional LED light.
- All-purpose vacuum cleaner ASR 35 L ACP: vacuum cleaner for liquids and dry solids with commercial registration. Particularly suited for extracting concrete and stone dust. AutoCleanPlus: save time and money with automatic MPulse filter cleaning in continuous use. User safety: certified in accordance with EU standard for dust class L.

Order no.  
EAN code

69088600  
4007430282699

### Scope of delivery


Long-neck Sander LSV 5-225 Comfort: sanding plate (very soft), 25 hook and loop sanding sheets with multi-perforation (P120), connecting sleeve, hexagonal wrench, plastic carry case. All-purpose vacuum cleaner ASR 35 L ACP with suction hose (Ø 35 mm / 3.2 m), handle adapter, 2 plastic suction tubes, 2 polyester filter cassettes (class M), PE filter bags, crevice nozzle, floor nozzle (370 mm wide)

**All-Purpose Vacuum Cleaner ASR 35 L ACP**



Air output max.	4380 l/min / 157 cfm
Vacuum	270 hPa (mbar) / 3.6 psi
Filter surface	8600 cm <sup>2</sup> / 1333 sq.inch
Input power max.	1400 W
Container volume	35 l / 9 gal
Suction hose Ø	35 mm / 1 3/8 "
Hose length	3.2 m / 11 ft
Weight	16 kg / 35.3 lbs
Cable length	8 m / 26 ft
	<ul style="list-style-type: none"> <li>• For extraction from the power tool in continuous mode, both on construction sites and in the workshop</li> <li>• Especially suited for extracting concrete and rock dust</li> <li>• Compact vacuum cleaner for liquids and dry solids with commercial registration</li> <li>• AutoCleanPlus: saves both costs and time thanks to automatic MPulse filter cleaning during continuous use</li> <li>• If the optimum suction performance falls below a certain level, the filters are vibrated immediately</li> <li>• User protection: certified in accordance with EU standard for L class dust</li> <li>• Automatic shut-down when vacuuming liquids once the maximum fill level is reached</li> <li>• Suction power control for adapted suction performance</li> <li>• Automatic trailing mechanism for emptying the suction hose completely</li> <li>• Antistatic basic equipment prevents static charge when using appropriate accessories</li> <li>• Sturdy thanks to especially large wheels and castors with wheel stop</li> <li>• Cable winding mechanism</li> <li>• Practical accessory case and storage area</li> </ul>

**Comfort Long-neck Sander LSV 5-225**

	Sanding disc diameter	225 mm / 8 7/8 "
	No-load speed	1000 - 1650 rpm
	Rated input power	500 W
	Output power	270 W
	Adjustable machine length	1.1 / 1.6 / 2.1 m // 41 3/8 / 61 7/32 / 81 1/16 "
	Weight (without power cable)	4.5 kg / 9.9 lbs
	Cable length	4 m / 157 1/2 "
		<ul style="list-style-type: none"> <li>• For convenient sanding of primed surfaces on walls or ceilings</li> <li>• Selectable LED side light to help detect imperfections and serrations and ensure a perfect finish.</li> <li>• Optimum balance when working, as the centre of gravity of the machine is not at the sanding head</li> <li>• Variable length adjustment: can be shortened or extended without tools for narrow rooms or high ceiling rooms</li> <li>• Extendable to a total length of 2.1 m with additional extension (accessory)</li> <li>• M-Clean technology: Effective extraction through the machine housing for maximum flexibility of the sanding head</li> <li>• Ideal adaptation of the flexible sanding head to the surface for good work results</li> <li>• Optimum extraction results thanks to spring-mounted brush rim that adapts to the surface.</li> <li>• Vario-Constamatic (VC)-Full wave electronics for working at customised speeds to suit the application materials, and speeds that remain almost constant even under load</li> <li>• Ergonomically shaped aluminium handle bar and T-handle for comfortable use in different positions</li> <li>• Simple, quick and tool-free exchangeable shaft can be adjusted directly on site if needed</li> <li>• Putting the machine down without kinking the hose and cable</li> <li>• With extensive range of grinding media for every application</li> <li>• Extraction possibility by means of connecting an all-purpose vacuum cleaner</li> </ul>