



## KH 5-40 Set with SDS-max chisel set (5 pieces)

- Combination hammer with 2 functions: hammer drilling and chiselling
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- Robust die cast aluminium gear housing for optimum heat dissipation and long service life

Order no.	691057000
EAN code	400743033278
Max. single blow energy (EP-TA)	7.1 J
Maximum impact rate	2800 bpm
Rated input power	1100 W
Drill-Ø concrete with hammer drills	40 mm / 1 9/16 "
Drill-Ø masonry with core bits	105 mm / 4 1/8 "
No-load speed	620 rpm
Bit retainer	SDS-max
Collar diameter	61 mm / 2.4 "
Weight (without power cable)	7.1 kg / 15.7 lbs
Cable length	4 m

### Scope of delivery

rubber-coated side handle, Drilling depth guide, Lubricant for tool shank end, Plastic carry case, SDS-max chiselling bit set (5 pieces)