



MKS 18 LTX 58 FS Set with guide rail FS 160

- Powerful cordless metal cutting circular saw with chip collection box for cold sawing of metals. Compatible with guide rails.
- Fast and precise cutting of tubes, profiles, channels, metal grids and sheets, free from sparks and burrs.
- With chip collection box for a clean working environment
- Robust saw with guard made from die-cast aluminium and stainless steel base plate
- Lower weight and compact, ergonomic design
- Viewing window in the guard for precise cutting guidance
- Cutting depth control, steplessly adjustable and without tools according to mm and inch scale
- Comfortable saw blade change with spindle lock
- Fast brake for highest safety with quick saw blade stop (< 1 sek)
- Precise straight cuts of metal grids, steel and profile sheets thanks to guide rail (accessory)
- With metaBOX, the intelligent solution for transport and storage

Order no.	691114000
EAN code	4061792156203

Battery voltage	18 V
Adjustable cutting depth	0 - 58 mm // 0 - 2.28 "
Maximum cutting depth at 90°	58 mm / 2.28 "
Saw blade Ø x bore	165 x 20 mm // 6 1/2 x 5/8 "
Max. cutting speed	31 m/s / 102 ft/min
Weight without battery pack	2.8 kg / 6.2 lbs
Weight with battery pack	3.7 kg / 8.2 lbs

Scope of delivery

Carbide circular saw blade for metal (40 teeth), Parallel guide, Hexagonal wrench, Guide rail FS 160 (160 cm), Guide rail adapter, metaBOX 340, without battery pack, without charger