



Set FSR 200 + FSX 200 with accessories

- Palm grip orbital sander FSR 200 Intec: Light and compact tool for comfortable one-hand operation, dust-protected ball bearings for high service life of the tool, dust collector cartridge with filter for working without connecting to a vacuum cleaner
- Palm grip random orbital sander FSX 200 Intec: Light and compact tool for comfortable one-hand operation, very good weight/performance ratio for low-fatigue working, dust-protected ball bearings for long service life of the machine, dust collector cartridge with filter for working without connecting a vacuum cleaner


Order no.
EAN code

69112500
4061792171084


Scope of delivery

FSX 200 Intec, FSR 200 Intec, 2 x plastic carry case, tool bag, 25 hook and loop sanding sheets 125 mm, 10 hook and loop sanding sheets 115x103 mm P 40


Palm Grip Random Orbital Sander FSX 200 Intec

	Diameter of backing pad	125 mm / 5 "
	Rated input power	240 W
	No-load speed	11000 rpm
	Orbital frequency with no load	22000 opm
	Orbit diameter	2.7 mm / 1/8 "
	Weight (without power cable)	1.3 kg / 2.9 lbs
	Cable length	2.8 m / 9 ft
		<ul style="list-style-type: none"> • Light and handy machine for convenient one-hand operation • Very good weight/performance ratio for low-fatigue working • Grip area with non-slip soft-grip surface • Dust-proof ball bearings for long service life of the machine • Dust collector cartridge with filter for working without connecting to a vacuum cleaner • Extraction possibility by means of connecting to an all-purpose vacuum cleaner via an adapter (accessory)

Palm Grip Random Orbital Sander FSX 200 Intec

	Diameter of backing pad	125 mm / 5 "
	Rated input power	240 W
	No-load speed	11000 rpm
	Orbital frequency with no load	22000 opm
	Orbit diameter	2.7 mm / 1/8 "
	Weight (without power cable)	1.3 kg / 2.9 lbs
		<ul style="list-style-type: none"> • Light and handy machine for convenient one-hand operation • Very good weight/performance ratio for low-fatigue working • Grip area with non-slip soft-grip surface • Dust-proof ball bearings for long service life of the machine • Dust collector cartridge with filter for working without connecting to a vacuum cleaner • Extraction possibility by means of connecting to an all-purpose vacuum cleaner via an adapter (accessory)

Palm Grip Orbital Sander FSR 200 Intec

	Base plate	114 x 102 mm (1/4 sheet)
	Rated input power	200 W
	No-load speed	13000 rpm
	Orbital frequency with no load	26000 opm
	Orbit diameter	1.4 mm / 1/16 "
	Weight (without power cable)	1.3 kg / 2.9 lbs
	Cable length	2.8 m / 9 ft
		<ul style="list-style-type: none"> • Light and handy machine for convenient one-handed operation • Very good weight/performance ratio, ideal for working overhead • Grip area with non-slip soft-grip surface • Dust-proof ball bearings for long service life of the machine • Robust clamping system for sanding paper with or without hook and loop fastener • Dust cartridge with filter for working without connecting to a vacuum cleaner • Extraction possibility by means of connecting to an all-purpose vacuum cleaner via an adapter (accessory)

Palm Grip Orbital Sander FSR 200 Intec



Base plate	114 x 102 mm (1/4 sheet)
Rated input power	200 W
No-load speed	13000 rpm
Orbital frequency with no load	26000 opm
Orbit diameter	1.4 mm / 1/16 "
Weight (without power cable)	1.3 kg / 2.9 lbs
	<ul style="list-style-type: none"> • Light and handy machine for convenient one-handed operation • Very good weight/performance ratio, ideal for working overhead • Grip area with non-slip soft-grip surface • Dust-proof ball bearings for long service life of the machine • Robust clamping system for sanding paper with or without hook and loop fastener • Dust cartridge with filter for working without connecting to a vacuum cleaner • Extraction possibility by means of connecting to an all-purpose vacuum cleaner via an adapter (accessory)