



## Set KS 66 FS with cross cutting rail KFS 44

- Robust circular saw, can be used directly on guide rails from Metabo and also Mafell, Bosch, Festool, Makita, HiKOKI, Hilti and other manufacturers
- Light guide plate made from die cast aluminium
- Fast, precise cross cuts thanks to easy coupling with a Metabo KFS cross cutting rail
- Grip area with non-slip soft-grip surface
- Clearly visible cutting indicator for precise sawing after initial cut
- 0° position re-adjustable for highest cutting precision
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Sawdust ejection nozzle for any working position can be rotated and locked individually
- Precision guide rail available as accessory

Order no.	69119600
EAN code	4061792200463
Rated input power	1500 W
Output power	840 W
Maximum cutting depth at 90°	66 mm / 2 5/8 "
Maximum cutting depth at 45°	47 mm / 1 7/8 "
Max. cutting depth with guide rail	61 mm / 2 13/32 "
Saw blade Ø x bore	190 x 30 mm // 7 1/2 x 1 3/16 "
Swivel range from / to:	0° / + 47°
No-load speed	5000 rpm
Speed at rated load	3800 rpm
Max. cutting speed	50 m/s
Weight (without power cable)	4.9 kg / 10.8 lbs

### Scope of delivery

Cross cutting rail KFS 44, Carbide circular saw blade (24 teeth), Parallel guide, Hexagonal wrench